



Solutions for a Safer Earth®

# Closed Loop Dispensing System

## Technical Data & Training Sheet



In order to meet the Green Seal™ GS-37 standard, TC 66 Tub & Tile Cleaner must be dispensed from one of these two closed loop dispensing systems. You can also use either of these dispensing systems with Safe 2 Clean, GC 55 and MP 11 as a closed loop system or as an open system. You must specify which type of dispensing system you prefer at the time you place an order.

### BLEND MATE WALL DISPENSER

#### PRODUCT DESCRIPTION:

A reusable mounted dispenser with the addition of a no spill cap system for automatic dilution/metering of our FOCUS Concentrate products into secondary containers (32 oz. bottle or bucket fill) in ready to use form.

#### USES:

Convenient wall mount in janitor's closets, housekeeping / maintenance rooms, etc.

#### SPECIFICATIONS:

APPEARANCE: Gray high density plastic cabinet

INSTALLATION MATERIALS INCLUDED: Mounting hardware, water inlet hose, 2 locking keys, appropriate metering tips installed by the factory according to product used.

CABINET SIZE: 22" high x 6 1/2" width x 7 3/4" depth.

Up to 4 cabinets can be linked together with a single cold water source.

#### DIRECTIONS FOR PRODUCT USE:

1. Hang cabinet on wall using mounting screws provided, making sure water hose will reach water source.
2. Connect black 6' water hose to upper right side of dispenser cabinet and water source.
3. Using key (s) provided, unlock cabinet.
4. Remove over cap from bottle of concentrate, tighten draw tube cap onto bottle by turning clockwise until secure and place bottle inside dispenser cabinet.
5. Close and lock cabinet.
6. Following direction label on front of dispenser, turn toggle switch to desired dilution strength. Insert clear plastic fill tube into spray bottle or mop bucket and push appropriate button to activate flow.



#### AVAILABLE FOR:

**TC 66 TUB & TILE CLEANER:** 2 button (32 oz. bottle & bucket fill), 3 dilution selector.

**MP 11 MULTI PURPOSE CLEANER:** 2 button (32 oz. bottle & bucket fill), 3 dilution selector

**GC 55 GLASS & WINDOW CLEANER:** 1 button (32 oz. bottle), pre-set dilution

**SAFE 2 CLEAN PEROXIDE CLEANER:** 2 button (32 oz. bottle & bucket fill), 2 dilution selector

### BLEND MATE DILUTION GUN

#### PRODUCT DESCRIPTION:

A portable closed loop dispensing system with the addition of a no spill cap insert for use with bottles of FOCUS concentrates. It provides the proper dilution into secondary containers (32 oz bottles or mop bucket) in ready to use form.

#### USES:

An economical, portable, reusable dispenser that can be used anywhere there is a convenient water source: basements, apartments, laundry rooms, janitor's closets, housekeeping/maintenance rooms, etc.

#### SPECIFICATIONS:

Durable plastic screw-on nozzle with PVC dispensing tube; 10' rubber hose provided for connection to water source. Self-venting drip-proof bottle insert prevents any potential spillage or contact with concentrate during assembly. A backflow attachment eliminates excess liquid from escaping gun or bottle. Blend Mate Dilution Guns for use with TC 66, MP 11 and Safe 2 Clean are pre-set for light duty and heavy duty dilutions (see individual product labels for corresponding light and heavy duty dilution ratios). The Blend Mate Dilution Gun for GC 55 is pre-set to dispense 2 oz. concentrate per gallon of water only.




1. Spill-proof insert is shown in neck of gallon bottle and Dilution Gun cap.



2. Attach Dilution Gun to gallon bottle by twisting cap clockwise until tightened.



3. Connect rubber hose to water source and attach to Dilution Gun twisting connector clockwise until tight.



4. Select light duty (red toggle A) or heavy duty (green toggle B) by twisting upward to plastic stop as shown. Twist black water flow (toggle C) forward to horizontal position to initiate flow. Dispense into 32 oz bottle or mop bucket.



#### MANUFACTURED BY:



39-30 Review Avenue  
Long Island City, New York 11101  
1-888 WAX PLUS • (718) 392-8080 Fax: (718) 482-9366  
Visit us on the web! [www.focus-accs.com](http://www.focus-accs.com)

